

XL5 PEDIATRIC MANUAL WHEELCHAIR

For Alberta Aids to Daily Living only

AADL #W116

Effective October 1, 2018



Date:	P.O.#:	Account#:
Made for (client):		
Ordered by:		
Organization:		
Address:		
Phone:	Fax:	

STANDARD SEAT-TO-FLOOR WILL BE SET AT 15 ½" BASED ON 20" OR 22" SPOKE WHEELS AND 6" CASTERS.

NOTE: ITEMS WITH THIS SYMBOL (▲) ARE NOT FUNDED BY AADL

XL5 PEDIATRIC MANUAL WHEELCHAIR	☐	\$2 395
FRAME COLOR		
Glossy Black ☐ Secure Blue ☐	←	N/C
SEAT WIDTH		
11" ☐ 12" ☐ 14" ☐ 16" ☐	←	N/C
SEAT DEPTH		
12" ☐ 14" ☐ 16" ☐	←	N/C
BACK HEIGHT (STRAIGHT CANE)		
16" ☐	←	STD
BACK POST		
Straight with Push Handle 0° ☐		STD
SEAT		
Standard Seat Sling ☐		STD
2" Seat Cushion ☐		N/C
BACK		
Standard Upholstery ☐		STD
ANGLE ADJUSTABLE BACKREST		
Back Angle -5° ☐ 0° ☐ 5° ☐ 10° ☐ 15° ☐	←	N/C
ANGLE ADJUSTABLE STROLLER BAR		
Angle Adjustable Stroller Bar (#13-00016) ☐		N/C
ARMREST		
« T » Type - Removable, Height Adjustable ☐		N/C
ARMPAD		
Full Length (#ST-02525) ☐		N/C
FOOTREST (ADJUSTABLE IN HEIGHT FROM 6" to 9")		
90° Swing Away - Desired Height : _____ " ☐		STD
70° Swing Away - Desired Height : _____ " ☐		STD

STANDARD FEATURES	
Color: Glossy Black/Secure Blue	Wheel Locks: Push to Lock
Weight Capacity: 250 lb	Axles: Threaded Axles
Frame: Standard and Hemi	Armrest: « T » Type
Seat Width: 11", 12", 14", 16"	Footrest: 70° and 90° Swing Away
Seat Depth: 12", 14", 16"	Handrim: Aluminium
Seat-to-Floor Height: 13" to 20 ½"	Transport Tie-Downs
Back Height: 16"	Anti Tip
Rear Wheels: 20", 22"	2" Seat Cushion
Urethane Front Wheel: 5", 6", 8"	

FOLDING FOOTPLATE		
Angle and Depth Adjustable (Width 4" x Depth 5") ☐		\$180 Pair
Angle and Depth Adjustable (Width 6" x Depth 6 ¾") ☐		\$180 Pair
Adjustable Length Heel Loops ☐		\$55 Pair
WHEEL LOCKS		
Push to Lock ☐		STD
Fixed Extension Handle ☐		\$40 Pair ▲
Telescopic Extension Handle ☐		\$60 Pair
AXLES TYPE		
Threaded Axles ☐		STD
Quick Release Axle ☐		\$105
REAR WHEELS		
20" ☐ 22" ☐	←	STD
ANTI TIP		
Anti Tip ☐		STD
HANDRIM		
Aluminium ☐		STD
Plastic Coated Handrim ☐		\$130 Pair ▲
POSITIONING STRAP		
Center-Pull Auto Style Hip Belt ☐		\$75 ▲
SPOKE GUARDS		
PR-000 Transparent Spoke Guards ☐		N/C

AADL EXCLUSION LIST

PEDIATRIC XL5 - NOT FUNDED OPTION LIST

- Fixed Extension Handle
- Plastic Coated Handrim
- Center-Pull Auto Style Hip Belt


FRONT SEAT TO FLOOR HEIGHT

SELECT DESIRED HEIGHT

XL5


Hemi Frame — Short Fork

	FRONT WHEEL DIAMETER		
POSITION	5"	6"	8"
A			
B	13 ☐	13 ½ ☐	
C	13 ½ ☐	14 ☐	
D	14 ☐	14 ½ ☐	15 ½ ☐




Standard Frame — Short Fork

	FRONT WHEEL DIAMETER		
POSITION	5"	6"	8"
A	15 ½ ☐		
B	16 ☐	16 ½ ☐	
C	16 ½ ☐	17 ☐	
D	17 ☐	17 ½ ☐	18 ½ ☐




Standard Frame — Long Fork

	FRONT WHEEL DIAMETER		
POSITION	5"	6"	8"
A	18 ☐	18 ½ ☐	19 ½ ☐
B	18 ½ ☐	19 ☐	20 ☐
C	19 ☐	19 ½ ☐	20 ½ ☐
D	19 ½ ☐	20 ☐	21 ☐




REAR FLOOR TO SEAT HEIGHT TABLE

REAR WHEEL DIAMETER XL5 <u>select desired height</u>		
POSITION	20"	22"
A	13 ☐	14 ☐
B	13 ½ ☐	14 ½ ☐
C	14 ☐	15 ☐
D	14 ½ ☐	15 ½ ☐
E	15 ☐	16 ☐
F	15 ½ ☐	16 ½ ☐
G	16 ☐	17 ☐
H	16 ½ ☐	17 ½ ☐
I	17 ☐	18 ☐
J	17 ½ ☐	18 ½ ☐



Note - The measures are for reference purposes only. They depend on the wheel diameter, tilt angle and the rear wheel axle location.

REFERENCE SCHEME





A: SEAT-TO-FLOOR HEIGHT : _____

B: REAR SEAT-TO-FLOOR HEIGHT: _____

REAR WHEEL POSITION

Choose the rear wheel desired position



NOTES

AADL EXCLUSION LIST

PEDIATRIC XL5 - NOT FUNDED OPTION LIST

- Fixed Extension Handle
- Plastic Coated Handrim
- Center-Pull Auto Style Hip Belt